

Specifications

EXAMINATIONS

Testing distance	33 cm, 40 cm, 57 cm, 100 cm, infinite
Test field size	5°
Test field brightness photopic	120 cd/m
Test field brightness mesopic without glare	0.032 cd/m
Test field brightness mesopic with glare	0.1 cd/m
Glare illumination	0.35 lx

ELECTRICAL PROTECTION

Protection level	EMVG/DIN EN 60601-1
Protection class	II

DIMENSION & ELECTRICAL REQUIREMENTS

Dimensions WDH	265 × 330 × 460 mm
Net. weight	7.1 kg
Voltage	230 V
Frequency	50/60 Hz
Rated input voltage	230 V, 50/60 Hz
Power consumption	40 VA

TEST SEQUENCES

- Vision screening test for general use (near and far): DIN 58220-P5, G25: DIN 58220-P5, G37: DIN 58220-P5,
- Mesopic contrast vision: DIN 58220-P7
- Road traffic related vision screening test: DIN 58220-P6 (Appendix FeV 6.1)
- Road traffic related vision screening test: DIN 58220-P6 (Appendix Fev 6.2)
- JAR-FCL3 vision test for pilots, class 2
- Paediatric vision screening with single optotypes

RODENSTOCK Instruments

Wiesbadener Strasse 21
90427 Nürnberg, Germany
Phone +49 (0)911 938 546 2777
Fax +49 (0)911 938 546 220
info@rodenstock-instruments.de
www.rodenstock-instruments.de

RODENSTOCK Instruments is a
business unit of TOMEY GmbH



2023/03 – subject to change without notice

Optional equipment

Take a look at the supplementary products in detail.



Optical Bars



Transportation case

RODENSTOCK Instruments



Making analysis
fashionable

R 30nykto

Vision Tester

The R 30nykto: Tune up your business



”

Portability of my equipment along with easy handling are essential for my work in occupational medicine. With the R 30nykto, I am ready to go anywhere in an instant.

“

What are your benefits?



Functionality

Several vision tests according to DIN 58220



Added value

G25, G37, and JAR-FCL 3 tests for special requirements



Safe operation

Remote operation via touchpad



Portable

Lightweight and compact design



Efficiency

Fast and reliable screening



Connection

GDT interface for connecting to patient software

Your digital partner
in consulting.

Outstanding features

Equipment

Touchpad and glare shield included

Distance adjustment

From 33 cm to infinite

Tiltable corpus

For a comfortable examination

Application interface

Clear and well-structured

Guided test sequences

Assists the operator



Remote operation
via tablet

